



3 Type

- A** Mounting from the back (threaded blind bore)
- B** Mounting from the operator's side

1

2

b	$l_1 \pm 0,25$	l_2 Type A	$l_3 \approx$ Type B	a	d_1 Type A	d_2 Type B	h_1	h_2 Type B	r	t min.
20	120	142	137	13	M 5	5,3	41	5	13	10
20	160	182	177	13	M 5	5,3	45	5	13	10

Specification

- Aluminum
 - plastic coated
 - black, RAL 9005, textured finish
 - silver, RAL 9006, textured finish
 - anodized, natural color
 - blank
 - tumbled

- **SW**
- **SR**
- **EL**
- **BL**

• Load rating information → Page 1456

• RoHS

4

Information

Cabinet U-handles GN 565.3 are manufactured from a bent aluminum profile. They are suitable for applications where lower lifting forces are required such as on lids or protective machine covers.

The countersunk holes of type B allow fixing with self tapping screws or countersunk rivets.

Due to the manufacturing process, **special designs** can be supplied even in relatively small quantities.

How to order

1	b
2	l_1
3	Type
4	Finish

GN 565.3-20-120-B-SW

