



ROSTFREI  
Inox  
Stainless  
Steel

**3 Type**

- A** Mounting from the back (threaded blind bore)
- B** Mounting from the operator's side

**1**

**2**

b		$l_1 \pm 0,25$	$l_2 \approx$	a	$d_1$ Type A	$d_2$ Type B	$h_1 \approx$	$h_2$	$t_1$ min.	$t_2$
GN 565.4	GN 565.9									
20	20	160	185	13	M 6	5,3	50	5	8	5
20	20	192	221	13	M 6	5,3	50	5	8	5
26	-	160	190	17	M 8	6,4	57	6	11	6
26	-	192	227	17	M 8	6,4	57	6	11	6

**Specification**

**GN 565.4**

Aluminum

- plastic coated
- black, RAL 9005, textured finish
- red, RAL 3000, textured finish
- silver, RAL 9006, textured finish
- anodized, natural color
- blank
- tumbled

- SW
- RS
- SR
- EL
- BL

**GN 565.9**

Stainless Steel

- AISI 304
- matte shot-blasted

**MT**

• Load rating information → Page 1456

• Stainless Steel characteristics → Page 1489

• RoHS

**4**

**Information**

The manufacturing process (bending) allows the production of **special lengths** in relatively small quantities.

see also...

- Arch handles GN 424.1 (Steel, Ø10) → Page 120
- Stainless Steel-Arch handles GN 424.5 (Ø10) → Page 120

How to order (Aluminum)

<b>1</b>	<b>b</b>
<b>2</b>	$l_1$
<b>3</b>	<b>Type</b>
<b>4</b>	<b>Finish</b>

**GN 565.4-20-160-B-RS**

How to order (Stainless Steel)

<b>1</b>	<b>b</b>
<b>2</b>	$l_1$
<b>3</b>	<b>Type</b>
<b>4</b>	<b>Finish</b>

**GN 565.9-20-192-A-MT**