



ELESA Original design BT-SST/SST-FP



3 Type

- D** with threaded through bore
- E** with threaded blind bore

1

2

2

d ₁	d ₂ Type D	d ₃ Type E	d ₄	h	k	t ₁ min. Type E	t ₂ Type D
20	M 5	M 5	11,5	16	10	5	12
25	M 6	M 6	16	19	11	8	14
32	M 8	M 8	17	22	13	10	16

Specification

- Plastic
Technopolymer (Polyamide PA)
- reinforced
- temperature resistant up to 130 °C
- black, matte finish
- Bushing
Stainless Steel AISI 303
- *Plastic characteristics* → Page 1483
- *Stainless Steel characteristics* → Page 1489
- RoHS

Information

- see also...
- *Knurled nuts GN 421* → Page 449

How to order

GN 590.5-32-M8-E

- 1 d₁
- 2 d₂
- 3 Type

