



**elesa**

ELESA Original design BT.S-p-INOX



Inox  
Stainless  
Steel

1

2

3

d <sub>1</sub>	d <sub>2</sub>	Length l			d <sub>3</sub>	h	k
20	M 5	10	16	-	12	16	10
25	M 6	16	20	30	16	19	11
32	M 8	16	20	30	17	22	13

### Specification

- Plastic  
Technopolymer (Polyamide PA)  
- reinforced  
- temperature resistant up to 130 °C  
- black, matt finish
- Threaded bolt  
Stainless Steel  
German Material No. 1.4305
- *Stainless Steel characteristics* → Page xx
- *Plastic characteristics* → Page xx
- **RoHS compliant**

### Information

see also...

- *Knurled screws GN 421* → Page xx

How to order

**GN 591.5-20-M5-16**

1	d <sub>1</sub>
2	d <sub>2</sub>
3	Length l