



Inch
Inch
sized
available

d ₁	d ₂ Plastic		Material				d ₃	d ₄	l ₁	l ₂	l ₃
	KU	KT	KT	KT	ST	ST					
14	-	-	M 6	-	-	-	8	11	28	10	0,5
18	M 6	-	M 6	-	M 6	-	10	15	40	12	2,5
21	M 6	M 8	M 6	M 8	M 6	M 8	10	17	50	13	2,5
22	M 6	M 8	M 6	M 8	-	-	10	18	56	13	2,5
23	M 8	M 10	M 8	M 10	M 8	M 10	13	19	65	14	2,5
26	M 8	M 10	M 8	M 10	M 8	M 10	13	21	80	16	2,5
28	M 10	-	M 10	-	M 10	-	13	22	90	16	2,5
31	M 12	-	-	-	M 12	-	14	25	102	20	2,5

Specification

- Plastic
Duroplast (Phenolic PF)
- temperature resistant up to 110 °C
- black, shiny finish
- Plastic
Technopolymer (Polypropylene PP)
- temperature resistant up to 80 °C
- black, matte
- black, shiny finish (only size 14)
- Steel
Plastic coated
black, textured finish
- Spindle
Steel
zinc plated, blue passivated
- *Plastic characteristics* → Page 1483
- RoHS

1

KU

KT

ST

Information

Steel revolving handles GN 598 are mainly used on safety handwheels to increase imbalance and thus avoid free wheeling.

see also...

- *Retractable handles GN 598.3 (with hold in both positions)* → Page 43

How to order

GN 598-KU-21-M8

1	Material
2	d ₁
3	d ₂