



ELESA Original design ERM.SST-p



1		2		3															
l <sub>1</sub>	d <sub>1</sub>			l <sub>2</sub>				d <sub>2</sub>	d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	h <sub>4</sub>		Stroke				
44	M 4	-	-	12	16	20	25	32	-	-	10	14,5	24,5	3,5	30	3,5			
44	M 5	M 6	-	12	16	20	25	32	40	50	10	14,5	24,5	3,5	30	3,5			
63	M 6	M 8	-	16	20	25	32	40	50	63	13,5	18	31	3,5	38	4			
78	M 8	M 10	M 12	20	25	32	40	50	63	80	16	21,5	36	3,5	46	4			
95	M 10	M 12	-	20	25	32	40	50	63	80	19	25	43	5	56	4			

**Specification**

- Handle  
Zinc die casting
- Plastic coated  
black, RAL 9005, textured finish ● **SW**  
orange, RAL 2004, textured finish ● **OS**  
red, RAL 3000, textured finish ● **RS**  
silver, RAL 9006, textured finish ● **SR**
- Threaded stud and retaining screw  
Stainless Steel AISI 303
- *Stainless Steel characteristics* → Page 1489
- RoHS

**Information**

Adjustable hand levers GN 602.1 like all the products of the Ergostyle® family are renowned for their good style but also their ergonomic shape.

The gently arched handle with a reinforced end of the lever gives the operator a good grip.

Pulling the lever disengages the serration and allows it to be turned in either direction to reach the ideal new location. On releasing the handle the serrations re-engage automatically.

see also...

- *Product family Ergostyle®* → Page 17
- *Adjustable hand levers GN 604.1*  
(Lever plastic, with screw in Stainless Steel) → Page 341

How to order

1	l <sub>1</sub>
2	d <sub>1</sub>
3	l <sub>2</sub>
4	Color

**GN 602.1-44-M6-32-SB**

