



ELESA Original design: ERX.p



1		2		3																	
l <sub>1</sub>	d <sub>1</sub>	l <sub>2</sub>										d <sub>2</sub>	d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	h <sub>4</sub>	Stroke			
30	M 5	-	-	10	16	20	-	-	-	-	-	-	-	-	12	15,5	29,5	6	30	3,5	
30	M 6	-	-	10	16	20	25	30	40	-	-	-	-	-	12	15,5	29,5	6	30	3,5	
44	M 5	-	-	10	16	20	-	-	-	-	-	-	-	-	12	15,5	29,5	6	32,5	3,5	
44	M 6	-	-	10	16	20	25	30	40	45	-	-	-	-	12	15,5	29,5	6	32,5	3,5	
63	M 6	-	-	10	16	20	25	30	35	40	50	-	-	-	15	19	37,5	8	43	4	
63	M 8	-	-	16	20	25	30	35	40	45	50	60	70	15	19	37,5	8	43	4		
63	M 10	-	-	20	40	50	60	-	-	-	-	-	-	15	19	37,5	8	43	4		
78	M 8	-	-	20	25	30	40	45	50	55	60	70	-	19	24,5	47	12	54	4		
78	M 10	-	-	20	25	30	35	40	50	60	70	-	-	19	24,5	47	12	54	4		
78	M 12	-	-	20	25	30	35	40	45	50	60	70	80	19	24,5	47	12	54	4		
95	M 12	M 16	-	30	50	70	-	-	-	-	-	-	-	21,5	26,5	54,5	13	64,5	4,5		
108	M 12	M 14	M 16	30	50	70	-	-	-	-	-	-	-	25	30	54,5	11	65,5	4,5		

**Specification**

- Handle  
Plastic  
Technopolymer (Polyamide PA)  
- glass fiber reinforced  
- temperature resistant up to 130 °C  
- black-gray, matte, similar RAL 7021
- Color of the releasing button (shiny):
  - **DSG** black-gray, RAL 7021
  - **DOR** orange, RAL 2004
  - **DGR** gray, RAL 7035
  - **DGB** yellow, RAL 1021
  - **DBL** blue, RAL 5024
  - **DRT** red, RAL 3000
  - **DGN** green, RAL 6017
- Threaded stud  
Steel zinc plated, blue passivated
- Plastic characteristics → Page 1483
- RoHS



**Information**

Adjustable hand levers GN 603, like all the products of the Ergostyle® range, are renowned for their good style but also their ergonomic shape.

They are like all adjustable hand levers ideal whenever parts have to be clamped in a confined space or in a particular lever position. The centre insert is connected to the lever via serrations which can easily be disengaged.

The releasing button offers an easy disengagement. Its use is limited to applications where dismantling of the lever for installation is not required.

see also...

- Product family Ergostyle® → Page 17
- Adjustable hand levers GN 603.1 (with releasing button, threaded stud Stainless Steel) → Page 345

How to order

1	l <sub>1</sub>
2	d <sub>1</sub>
3	l <sub>2</sub>
4	Color of the releasing button

**GN 603-63-M8-20-DOR**

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4

