



ELESA Original design ERZ.



<b>1</b> $l_1$	<b>2</b> $d_1$ Thread			<b>2</b> $d_2$ H7 Bore		$d_3$	$d_4$	$h_1$	$h_2$	$h_3$	$h_4$ Stroke	$t$ min.
44	M 4	M 5	M 6	B 5	B 6	10	15,5	24,5	3,5	30,5	3,5	8
63	M 6	M 8	-	B 8	-	13,5	19	31	3,5	38,5	4	10
78	M 8	M 10	M 12	B 8	B 10	16	23	36	3,5	46,5	4	14
95	M 10	M 12	-	B 12	-	19	26,5	43	5	56,5	4	17

**Specification**

- Handle  
Plastic  
Technopolymer (Polyamide PA)  
- glass fiber reinforced  
- temperature resistant up to 130 °C  
- black-gray, RAL 7021



- orange, RAL 2004
- Annular gear ring  
Zinc die casting
- Bushing and retaining screw  
Steel, blackened
- ISO-Fundamental tolerances → Page 1479
- Plastic characteristics → Page 1483
- RoHS



**Information**

Adjustable hand levers GN 604 like all the products of the Ergostyle® family are renowned for their good style but also their ergonomic shape.

Pulling the lever disengages the serration and allows it to be turned in either direction to reach the ideal new location. On releasing the handle the serrations re-engage automatically.

see also...

- Product family Ergostyle® → Page 17
- Adjustable hand levers GN 604.1 (Plastic, bushing Stainless Steel) → Page 340

How to order

**GN604-44-M6-SG**

- 1**  $l_1$
- 2**  $d_1$  ( $d_2$ )
- 3** Color