



ELESA Original design ERZ.p



1		2		3													
l_1	d_1			l_2				d_2	d_3	h_1	h_2	h_3	h_4 Stroke				
44	M 4	-	12	16	20	25	32	-	-	-	10	15,5	24,5	3,5	30,5	3,5	
44	M 5	M 6	12	16	20	25	32	40	50	-	10	15,5	24,5	3,5	30,5	3,5	
63	M 6	M 8	12	16	20	25	32	40	50	63	13,5	19	31	3,5	38,5	4	
63	M 10	-	20	25	32	40	50	63	80	-	13,5	19	31	3,5	38,5	4	
78	M 8	M 10	16	20	25	32	40	50	63	80	16	23	36	3,5	46,5	4	
78	M 12	-	20	25	32	40	50	63	80	-	16	23	36	3,5	46,5	4	
95	M 10	M 12	16	20	25	32	40	50	63	80	19	26,5	43	5	56,5	4	
95	M 16	-	25	32	40	50	63	80	-	-	19	26,5	43	5	56,5	4	

Specification

- Handle
Plastic
Technopolymer (Polyamide PA)
- glass fiber reinforced
- temperature resistant up to 130 °C
- black-gray, RAL 7021
- orange, RAL 2004
- Annular gear ring
Zinc die casting
- Threaded stud and retaining screw
Steel
- Tensile strength class 5.8
- blackened
- *Strength values of screws* → Page 1481
- *Plastic characteristics* → Page 1483
- RoHS



Information

Adjustable hand levers GN 604, like all the products of the Ergostyle® family are renowned for their good style but also their ergonomic shape.

Pulling the lever disengages the serration and allows it to be turned in either direction to reach the ideal new location. On releasing the handle the serrations re-engage automatically.

see also...

- *Product family Ergostyle®* → Page 17
- *Adjustable hand levers GN 604.1 (Plastic, threaded stud Stainless Steel)* → Page 333

How to order

1	l_1
2	d_1
3	l_2
4	Color

GN 604-95-M12-25-SG

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

