



ELESA Original design M.843



Length l	a	b	d	h	t min.
86 ±0,5	17	26	M 6	46,5	12
117 ±0,5	20	30	M 8	53	13
179 ±1,0	20	30	M 8	62	13
300 ±1,0	22	32	M 8	64	13

Specification



- Plastic
Technopolymer (Polyamide PA)
temperature resistant up to 120 °C
- Colors (shiny finish):

black, RAL 9005	● SW
orange, RAL 2004	● OR
red, RAL 3000	● RT
white, RAL 9002, Cleanline	○ CL
yellow, RAL 1021	● GB
gray, RAL 7035	● GR
blue, RAL 5024	● BL
- Bushing
 - Standard: Brass
 - Cleanline (CL): Stainless Steel
- Strength properties → Page 1449
- Plastic characteristics → Page 1483
- RoHS

Information

GN 625 cabinet U-handles are renowned for their well proven elliptical extrusion profile as well as the ergonomic design with their smooth and shiny surface.

see also...

- Product family Cleanline → Page 17
- Cabinet U-handles GN 565 (Aluminum) → Page 80
- Cabinet U-handles GN 725 (Plastic) → Page 84

How to order

GN625-117-RT

- | | |
|---|----------|
| 1 | Length l |
| 2 | Color |

