



Length l	a	b	d	h	t min.
86 ±0,5	17	26	M 6	46,5	12
117 ±0,5	20	30	M 8	53	13
179 ±1,0	20	30	M 8	62	13
300 ±1,0	22	32	M 8	64	13

Specification

- Plastic
Technopolymer (Polyamide PA)
Temperature resistant up to 120 °C

Colors (shiny finish):

Black, RAL 9005

Orange, RAL 2004

Red, RAL 3000

Yellow, RAL 1021

Gray, RAL 7035

Blue, RAL 5024

Green, RAL 6017

White, RAL 9002

● SW

● OR

● RT

● GB

● GR

● BL

● GN

● WS

- Threaded bushing
 - Standard: Brass
 - Color white (WS): Stainless steel

• *Strength Properties* → Page 2116

• *Plastic Characteristics* → Page 2158

• RoHS



Information

Cabinet U-handles GN 625 have a very ergonomic elliptical profile and the surface is smooth and shiny.

see also...

- *Cabinet U-Handles GN 565 (Aluminum)* → Page 106
- *Cabinet U-Handles GN 725 (Plastic)* → Page 110

How to order

GN625-117-RT

1 Length l

2 Color