



d ₁	d ₂	d ₃	l ₁	l ₂	l ₃ min.
M 10	18	8	80	60	20
M 12	20	10	100	70	25
M 16	24	12	120	85	35
M 20	30	16	140	95	40

Specification

- Steel
Tensile strength class 5
blackened
- *Strength values of nuts* → Page 1481
- RoHS

Information

- see also...
- *Quick release toggle nuts GN 6305.1 (Steel, zinc plated)* → Page 376

How to order

DIN 6305-M16

1 d₁