



ROSTFREI
Inox
Stainless
Steel

2		3		4		4										d4	h1	h2
d1	d2	Length l ≈ GN 6335.4						Length l ≈ GN 6335.5										
32	M 6	16	20	25	30	35	45	-	-	-	-	-	-	12	20	9		
40	M 8	15	20	25	30	40	55	20	25	30	40	-	14	25	13			
50	M 10	25	30	35	45	55	-	20	25	30	45	55	18	32	18			
63	M 12	30	35	40	50	60	-	30	40	50	-	-	20	40	23			
80	M 16	30	40	50	60	70	-	-	-	-	-	-	25	50	28			

Specification

- GN 6335.4**
 - Threaded stud
Steel blackened
 - Knob
Cast iron
fettled and tumbled

SG
- GN 6335.5**
 - Threaded stud
Stainless Steel AISI 303
 - Knob
Stainless Steel precision casting
AISI CF-8
matte shot-blasted
 - Knob
Aluminum, forged
matte (ground)
polished

ES
AM
AP

- The threaded stud is screwed in and secured by a cross-dowel.
- *Stainless Steel characteristics* → Page 1489
- **RoHS**

Information

- see also...
- *Hand knobs 6335.4 (Plastic, threaded stud steel)* → Page 423
 - *Hand knobs 6335.5 (Plastic, threaded stud Stainless Steel)* → Page 423
 - *Stainless Steel-Star knobs GN 5334 / GN 5334.4* → Page 414
 - *Stainless Steel-Wing screws GN 433* → Page 440
 - *Stainless Steel-Wing screws GN 835* → Page 437

How to order (Threaded stud steel)

GN6335.4-SG-50-M10-35

1	Material
2	d1
3	d2
4	Length l

How to order (Threaded stud Stainless Steel)

GN6335.5-AP-40-M8-20

1	Finish (Material)
2	d1
3	d2
4	Length l