



ROSTFREI Rostfrei  
Inox Stainless Steel  
Inch sizes available

- 4 Type**
- A** without bore (unmachined)
  - B** with through bore H7
  - C** with blind bore H7
  - D** with threaded through bore
  - E** with threaded blind bore

2			3		3							
d <sub>1</sub>			d <sub>2</sub>	d <sub>3</sub>	d <sub>4</sub>	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	h <sub>4</sub>	t <sub>1</sub>	t <sub>2</sub>	
GG	NI	AL	Thread Type D Type E	H7 Bore Type B Type C		Type B, C, D, E	Type B, C, D, E	Type A	Type A	min.		
32	32	-	M 6	B 6	12	20	9	21	10	12	10	
40	40	40	M 8	B 8	14	25	13	26	14	15	13	
50	50	50	M 10	B 10	18	32	18	34	20	18	16	
63	63	63	M 12	B 12	20	40	23	42	25	22	20	
80	-	80	M 16	B 16	25	50	28	52	30	28	20	
100*	-	-	M 20	B 20	32	63	36	65	38	36	25	

\* not available in version ZB

**Specification**

- Cast iron** **GG**
  - fettled and tumbled
  - zinc plated, blue passivated
  - Thread: screw mobility only types D and E
- Stainless Steel** **NI**
  - Precision casting only types A, D, E
  - AISI CF-8
  - matte shot-blasted
- Aluminum** **AL**
  - forged
  - only Types A, C, D, E
  - matte finish (ground)
  - flash mark not visible
  - polished **MT**
- Metric ISO thread DIN 13** → Page 1477 **PL**
- ISO-Fundamental tolerances** → Page 1479
- Stainless Steel characteristics** → Page 1489
- RoHS**

**On request**

- plastic coated

**Information**

- see also...
- Hand knobs DIN 6335 (Plastic) → Page 422
  - Hand knobs GN 6335.1 (Duroplast, with protruding steel bushing) → Page 424
  - Hand knobs GN 6335.2 (Technopolymer, with protruding steel bushing) → Page 424
  - Hand knobs DIN 6335 with loss protection GN 111.7 → Page 1426

How to order (without bore, matte)	1 Material
<b>DIN 6335-AL-63-A</b>	2 d <sub>1</sub>
	4 Type

How to order (Cast iron)	1 Material
<b>DIN 6335-GG-63-M12-D</b>	2 d <sub>1</sub>
	3 d <sub>2</sub> (d <sub>3</sub> )
	4 Type

How to order (Aluminum)	1 Material
<b>DIN 6335-AL-50-B10-C-MT</b>	2 d <sub>1</sub>
	3 d <sub>3</sub> (d <sub>2</sub> )
	4 Type
	5 Finish