



Rostfrei INOX
Stainless Steel

- 4 Type**
- A** only with retaining ring
 - H** with retaining cable
 - K** with ball chain

d₁	d₂	Length l					d₃	h₁	h₂	h₃	r	s	t
25*	M 5	10	15	20	25	12	16	8	2,5	21,2	2,8	-	
32	M 6	16	20	25	30	14	20	10	3,5	22,3	2,8	12	
40	M 8	20	25	30	40	18	25	13	4	29,5	3,2	14	
50	M 10	20	25	30	45	22	32	17	5	34,6	3,8	18	
63	M 12	30	40	50	-	26	40	21	5,5	36,7	3,8	22	

* This size is only available with threaded stud.

Specification

- Star knob DIN 6336
Plastic
Technopolymer (Polyamide PA)
black, matte
- Bushing
Stainless Steel AISI 303
- Threaded stud
Stainless Steel
- M5 ... M10: 304 Cu
- M12: AISI 303
- Retaining ring GN 111.6
Stainless Steel AISI 301
- Ball chain GN 111.5 (Type K)
Stainless Steel AISI 301
- Retaining cable GN 111.2 (Type H)
Stainless Steel
coated with clear plastic
- RoHS

On request

- Ball chains / Retaining cables with other lengths
- with spiral retaining cable GN 111.4
- other GN standards with loss protection

Information

Star knobs GN 6336.13 can be captive-attached to a base element with the help of a ball chain or a retaining cable.

The star knobs are supplied ready assembled (with retaining ring and ball chain or retaining cable).

see also...

- *Stainless Steel-Ball chains GN 111.5* → Page 876
- *Retaining cables GN 111.2* → Page 877
- *Spiral retaining cables GN 111.4* → Page 878
- *Retaining rings GN 111.6* → Page 879
- *Further star knobs with loss protection GN 111.7* → Page 1426

How to order (Bushing)	
1 d₁	1 d₁
2 d₂	2 d₂
4 Type	4 Type
GN 6336.13-40-M8-A	

How to order (Threaded stud)	
1 d₁	1 d₁
2 d₂	2 d₂
3 Length l	3 Length l
4 Type	4 Type
GN 6336.13-50-M10-30-K	

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

