



4 Type

- D** With threaded through bore
- E** With threaded blind bore

2 d_1	3 d_2	d_3	h_1	h_2	t_1 min.	t_2
32	M 6	12	20	9	12	10
40	M 8	14	25	12	15	13
50	M 10	18	32	15	18	16
63	M 12	20	40	19	22	20

Specification

- Stainless steel precision casting **A4**
- AISI 316 **PL**
- Polished
- *Stainless Steel Characteristics* → Page 2166
- **RoHS**

Information

Stainless steel star knobs GN 6336 satisfy the dimensions of the DIN 6336 but differ in terms of their non-scooping geometry, which makes cleaning easier and helps prevent possible build-up of dirt.

They are suitable for areas with special hygiene requirements and, thanks to the material used, for applications in highly corrosive environments.

see also...

- *Star Knobs DIN 6336 (Plastic)* → Page 544
- *Star Knobs DIN 6336 (Cast Iron / Stainless Steel / Aluminum)* → Page 540
- *Star Knobs GN 6336.1 (Duroplast, with Protruding Bushing)* → Page 546
- *Star Knobs GN 6336.2 (Technopolymer, with Protruding Bushing)* → Page 546

<p>How to order</p> <p>GN 6336-A4-50-M10-D-PL</p>	1 Material
	2 d_1
	3 d_2
	4 Type
	5 Finish