



Rost **frei** **Inox** **Stainless** **Steel** **Inch** **sizes** **available**

4 Type

- A** without bore (unmachined)
- B** with plain through bore H7
- C** with plain blind bore H7
- D** with threaded through bore
- E** with threaded blind bore

2			3		3		d ₄	h ₁	h ₂ min.	h ₃	h ₄ min.	t ₁		t ₂
d ₁	GG	NI	AL	Thread	Bore	GG						AL	NI	
32	32	-	M 6	-	B 6	-	12	20	9	21	10	12	12	10
40	40	40	M 8	-	B 8	-	14	25	12	26	13	15	15	13
50	50	50	M 8	M 10	B 8	B 10	18	32	15	34	17	18	18	16
63	63	63	M 10	-	-	-	20	40	19	42	21	22	18	20
63	63	63	M 12	-	B 10	B 12	20	40	19	42	21	22	22	20
80	-	80	M 12	M 16	B 12	B 16	25	50	23	52	25	28	-	20

Specification

- Cast iron **GG**
 - fettled and tumbled
 - zinc plated, blue passivated
 - Thread: screw mobility only types D and E
- Stainless Steel-Precision casting **NI**
 - only types A, D, E
 - AISI CF-8
 - matte shot-blasted
- Aluminum **AL**
 - forged
 - only types A, C, D, E
 - matte finish (ground)
 - flash mark not visible
 - polished
- Metric ISO thread DIN 13 → Page 1477
- ISO-Fundamental tolerances → Page 1479
- Stainless Steel characteristics → Page 1489
- RoHS
- On request**
 - plastic coated

Information

- see also...
- Star knobs DIN 6336 (Plastic) → Page 398
 - Star knobs GN 6336.1 (Duroplast, with protruding steel bushing) → Page 400
 - Star knobs GN 6336.2 (Technopolymer, with protruding steel bushing) → Page 400
 - Star knobs DIN 6336 with loss protection GN 111.7 → Page 1426

How to order (without bore, matte)	1 Material
DIN 6336-AL-50-A	2 d ₁
	4 Type

How to order (Cast iron)	1 Material
DIN 6336-GG-63-M12-D	2 d ₁
	3 d ₂ (d ₃)
	4 Type

How to order (Aluminum)	1 Material
DIN 6336-AL-40-B8-C-PL	2 d ₁
	3 d ₃ (d ₂)
	4 Type
	5 Finish