



ROSTFREI Rost frei
Inox Stainless Steel
Inch sizes available

4 Type

K with threaded bushing
D with threaded through bore

2

3

d ₁	d ₂			Bushing MS Plastic KU Type K	Bushing NI Plastic KU / KT Type K	d ₃	h ₁	h ₂	t ₁ min.	t ₂	
	Bushing steel Plastic KU Type K	Plastic KT Type K	Plastic KT Type D							Bushing steel Bushing MS Bushing NI (KT)	Bushing NI (KU)
20	-	-	-	M 4	-	10	13	7	6,5	-	-
25	-	M 4	-	-	-	12	16	8	7,5	-	-
25	M 5	M 5	-	M 5	M 5	12	16	8	9,5	7,5	-
25	-	M 6	-	-	-	12	16	8	9	-	-
32	-	M 4	-	-	-	14	20	10	6,5	-	-
32	-	M 5	-	-	M 5	14	20	10	9,5	7,5	-
32	M 6	M 6	M 6	M 6	M 6	14	20	10	12	9	10,5
40	M 6	M 6	-	M 6	M 6	18	25	13	12	9	-
40	M 8	M 8	M 8	M 8	M 8	18	25	13	14	12	13
40	-	M 10	-	-	-	18	25	13	14	-	-
50	M 8	M 8	M 8	M 8	M 8	22	32	17	14	12	16
50	M 10	M 10	M 10	M 10	M 10	22	32	17	18	15	16
50	-	M 12	-	-	-	22	32	17	18	-	-
63	M 10	M 10	-	M 10	M 10	26	40	21	18	15	-
63	M 12	M 12	M 12	M 12	M 12	26	40	21	22	18	20
63	-	M 16	-	-	-	26	40	21	22	-	-
80	M 12	M 12	-	M 12	M 12	35	50	25	22	18	-
80	M 16	M 16	-	M 16	M 16	35	50	25	30	24	-

Specification

1

5

- Plastic
 - Duroplast (PF) **KU**
 - black, shiny
 - Bushing
 - Steel, zinc plated, blue passivated **MS**
 - Brass **NI**
 - Stainless Steel AISI 304
- Plastic
 - Technopolymer (Polyamide PA) **KT**
 - shock-resistant
 - black, matte
- Bushing
 - Steel, zinc plated, blue passivated **MS**
 - Stainless Steel AISI 303 **NI**
- Plastic characteristics → Page 1483
- Stainless Steel characteristics → Page 1489
- RoHS

Information

Star knobs DIN 6336 with bore H7 are available as GN 6336.1 and GN 6336.2.

see also...

- Star knobs GN 6336 (Cast iron / Stainless Steel / Aluminum) → Page 396
- Star knobs GN 6336.1 (Duroplast, with protruding bushing steel) → Page 400
- Star knobs GN 6336.2 (Technopolymer, protruding bushing steel) → Page 400
- Star knobs GN 6336.13 (with loss protection) → Page 405

Bestellbeispiel (Duroplast, bushing Steel)

1 Material

2 d₁

3 d₂

4 Type

DIN 6336-KU-63-M12-K

How to order (Technopolymer, bushing St. Steel)

1 Material

2 d₁

3 d₂

4 Type

5 Bushing

DIN 6336-KT-50-M10-K-NI