



ELESA Original design EWN



3 Type

E with threaded blind bore (cover cap)

D with threaded through bore

d ₁	d ₂ GN 634			d ₂ GN 634.1		d ₃	d ₄	d ₅	b	h ₁	h ₂	h ₃	h ₄
48	M 5	M 6	M 8	M 6	M 8	13,5	8,5	10	7	24	5,5	12	22
55	M 6	M 8	-	M 8	-	16	10,5	12	8	28	6,5	18	25
63	M 8	M 10	-	M 10	-	19	10,5	14	9	32	7,5	20	29
70	M 8	M 10	-	M 10	-	20	13	15	10	36	8	20	32

Specification

- Plastic
Technopolymer (Polyamide PA)
- glass fiber reinforced
- temperature resistant up to 130 °C
- black-gray, matte similar to RAL 7021

• **GN 634**
Bushing brass

• **GN 634.1**
Bushing Stainless Steel AISI 303

- Color of the cover cap (matte):
black-gray, RAL 7021
orange, RAL 2004
gray, RAL 7035
yellow, RAL 1021
blue, RAL 5024
red, RAL 3000



- *Plastic characteristics* → Page 1483
- *Stainless Steel characteristics* → Page 1489
- **RoHS compliant**

On request

- all in Stainless Steel

Information

Design and handling of the wing nuts GN 634 / GN 634.1 comply with the requirements and claims of the Ergostyle® product family.

see also...

- *Product family Ergostyle®* → Page 17
- *Wing nuts GN 640 (with smaller diameter)* → Page XYZ
- *Clamping elements GN 826 (for adjustable spindles)* → Page 268

How to order (Bushing brass)

GN 634-55-M8-E-DSG

1	d ₁
2	d ₂
3	Type
4	Color of the cover cap

How to order (Bushing Stainless Steel)

GN 634.1-55-M8-E-DSG

1	d ₁
2	d ₂
3	Type
4	Color of the cover cap