



ELESA Original design CWN.p

1.1

1.2

1.3

1.4

1

2

3

d <sub>1</sub>	d <sub>2</sub>	Length l				d <sub>3</sub>	b	h <sub>1</sub>	h <sub>2</sub>
32	M 4	10	16	-	-	12	6	16,5	3,5
32	M 5	10	16	20	-	12	6	16,5	3,5
32	M 6	10	16	20	25	12	6	16,5	3,5
40	M 8	16	20	25	30	13,5	6,5	21	4,5

2.1

Specification

- Plastic  
Technopolymer (Polyamide PA)  
- glass fiber reinforced  
- temperature resistant up to 130 °C  
- black, matte finish
- Threaded stud  
Steel  
zinc plated, blue passivated
- Plastic characteristics → Page 1483
- RoHS

Information

- see also...
- Wing screws GN 633 (with bigger diameter d<sub>1</sub>) → Page XYZ
  - Wing screws GN 531 → Page 433
  - Wing screws GN 531.1 → Page 435

2.2

2.3

2.4

How to order

GN 639-40-M8-20

1	d <sub>1</sub>
2	d <sub>2</sub>
3	Length l

