



1.1

1.2

1.3

1.4

1

2

b_1	$l_1 \pm 0,25$	a	b_2	d	h -1	$l_2 \approx$	l_3	$l_4 \approx$
26	350	17	14	M 8	69	526	328	17
26	450	17	14	M 8	69	632	428	20

2.1

Specification

3

- Arch handle
 - Aluminum
 - plastic coated
 - black, RAL 9005, textured finish ● **SW**
 - silver, RAL 9006, textured finish ● **SR**
- End pieces (for SW and SR)
 - Zinc die casting
 - plastic coated
 - silver, RAL 9006, textured finish
- Grub screw
 - Steel, tensile strength class 5.8
 - zinc plated, blue passivated
- Hexagon nuts ISO 4032-M8
 - Steel, zinc plated
- Washers DIN 125
 - Steel, zinc plated
- Load rating information → Page 1456
- RoHS

Information

see also...

- Cabinet U-handles GN 428 (Aluminum) → Page 117

2.2

2.3

2.4

How to order

GN 665-26-450-SW

1	b_1
2	l_1
3	Finish

