



Rostfrei  
Inox  
Stainless  
Steel

**3 Type**

- A** without knurl
- B** with knurl

<b>1</b> $d_1$	<b>2</b> $d_2$	$d_3$	$h_1$	$h_2$	$t$ min.
21	M 4	12,5	18	10,5	10
21	M 5	12,5	18	10,5	10
25	M 6	14,5	22,5	14	12
25	M 8	14,5	22,5	14	12
31	M 8	18,5	27	17	15
31	M 10	18,5	27	17	17

**Specification**

- **GN 676.1**  
Steel  
blackened
- **GN 676.5**  
Stainless Steel AISI 303  
matte shot-blasted
- *Stainless Steel characteristics* → Page 1489
- **RoHS**

**Information**

Knobs GN 676.1 / GN 676.5 are used in applications where a push or pull movement is required. Their concave top gives a more comfortable thumb grip.

The knurled model (Type B) can be used as an attractively shaped knurled knob with a threaded blind hole.

see also...

- *Knurled knobs GN 676* → Page 62
- *Waist shaped knobs GN 75* → Page 59
- *Waist shaped Stainless Steel-Knobs GN 75.5* → Page 59

How to order (Steel) <b>GN676.1-21-M5-B</b>	<b>1</b> $d_1$
	<b>2</b> $d_2$
	<b>3</b> Type

How to order (Stainless Steel) <b>GN676.5-31-M10-A</b>	<b>1</b> $d_1$
	<b>2</b> $d_2$
	<b>3</b> Type