



ROSTFREI
Inox
Stainless
Steel

- 3 Type**
- A Without knurl
 - B With knurl

1 d ₁	2 d ₂	d ₃	h ₁	h ₂	t min.
21	M 4	12,5	18	10,5	10
21	M 5	12,5	18	10,5	10
25	M 6	14,5	22,5	14	12
25	M 8	14,5	22,5	14	12
31	M 8	18,5	27	17	15
31	M 10	18,5	27	17	17

Specification

- **GN 676.1**
Steel
Blackened
- **GN 676.5**
Stainless steel AISI 303
Matte shot-blasted
- *Stainless Steel Characteristics* → Page 2166
- **RoHS**

Information

Knobs GN 676.1 / GN 676.5 are used in applications where a push or pull movement is required. Their concave top gives a more comfortable thumb grip.

The version with knurl (Type B) can be used as a knurled nut.

see also...

- *Knurled Knobs GN 676* → Page 84
- *Knurled Knobs GN 676 (Detectable Plastics)* → Page 86
- *Knurled Knobs GN 676 (Antibacterial Plastic)* → Page 87
- *Waist Shaped Knobs GN 75* → Page 82
- *Waist Shaped Stainless Steel Knobs GN 75.5* → Page 82

How to order (Steel) GN 676.1-21-M5-B	1 d ₁
	2 d ₂
	3 Type

How to order (Stainless steel) GN 676.5-31-M10-A	1 d ₁
	2 d ₂
	3 Type