



**3 Type**

- A** Flat spindle tip
- B** Rounded spindle tip

d <sub>1</sub>	Länge l			d <sub>2</sub>	d <sub>3</sub>	h	m	r
M 4	33	43	-	8	8	10	2,2	6
M 5	45	55	-	10	9	11	2,7	8
M 6	35	55	65	13	12	12	3,2	10
M 8	43	68	-	16	14	18	4	12
M 10	50	77	97	20	18	21	5	15
M 12	100	130	-	25	23	24	6	18

**Specification**

- Spindle
  - Steel **ST**  
zinc plated, blue passivated
  - Stainless Steel AISI 304 **NI**
- Hexagon nuts ISO 4035
  - Steel
  - zinc plated, blue passivated
  - Stainless Steel AISI 304
- Pressure pad
  - Rubber, Neoprene (CR)
  - 85 Shore A ≈
  - vulcanized
  - black
- *Stainless Steel characteristics* → Page 1489
- *Elastomer characteristics* → Page 1483
- RoHS



**Information**

The two hexagon nuts are included parts of the order.

see also...

- *Holders for clamping screws GN 809*  
(for toggle clamps with solid clamping arm) → Page 591
- *Holders for clamping screws GN 801*  
(for toggle clamps with forked clamping arm) → Page 590

How to order (Steel)

**GN 708.1-M8-43-B-ST**

- 1 d<sub>1</sub>
- 2 Length l
- 3 Type
- 4 Material

How to order (Stainless Steel)

**GN 708.1-M5-45-A-NI**

- 1 d<sub>1</sub>
- 2 Length l
- 3 Type
- 4 Material

