



**3 Type**

- A** with friction ring
- B** without friction ring

2 Bores for socket head cap screws DIN 912

<sup>1</sup> $d_0$ Control knob Ø GN 723.4	$d_1$	<sup>2</sup> $d_2$ H8		$d_3$ -0,1	$d_4$	$k$	$l_1$	$l_2$
27	33,5	B 6	-	23,3	3,4	13	11,2	4
34	41	B 6	B 8	29,3	3,4	18	14,2	5
42	50	B 8	B 10	37,3	4,5	24	16,2	5

**Specification**

- Aluminum  
anodized, black
- Reference arrow  
white, engraved with laser precision
- Clamp ring  
Rubber
- Friction ring  
Polyamide
- ISO-Fundamental tolerances → Page 1479
- RoHS

**Information**

Reference flanges GN 723.3 are used together with control knobs GN 723.4 which offer the following advantages:

- they have a reference mark to line up with the control knob scale,
- they offer additional support for the control shaft,
- the version with friction ring prevents an unexpected movement of the control knob by vibration.

see also...

- Control knobs GN 723.4 (Aluminum) → Page 264

How to order

**GN 723.3-50-B8-A**

- <sup>1</sup>  $d_1$
- <sup>2</sup>  $d_2$
- <sup>3</sup> Type