



Arrow resp. 0 in case of graduation opposite grub screw



3 Type

- A with arrow
- B neutral, without indicator point or scale
- S with scale 0...9
20 graduations

4 Identification no.

- 1 with grub screw
- 2 with collet

1

2

2

d ₁	d ₂ H8 Bore		d ₃ Collet	d ₄	d ₅	d ₆	d ₇	h ₁	h ₂	h ₃	h ₄	l	t
22	B 5	-	-	16	14	M 4	27,5	22	16	4,3	8	12,5	-
27	B 6	-	Z 6	20	18	M 4	33,5	26	20	4,3	9	14	14
34	B 6	B 8	Z 8	25	23	M 5	41	30	24	4,2	10	15	17
42	B 8	B 10	Z 10	32	30	M 5	50	34	28	4	11	16	20

Specification

- Aluminum
anodized, black
- Scale ring
Plastic, black
pressed on
- Arrow (Type A)
and scale (Type S)
white, engraved with laser precision
- Cover
Plastic, light gray
- Collet / hexagon nut
Brass
- Stainless Steel-Grub screw DIN 916
with internal hexagon and serrated point
- ISO-Fundamental tolerances → Page 1479
- RoHS

On request

- special graduations
see „How to order Graduations“ → Page 252

Information

The light gray cover of the control knobs GN 726.2 shrouds the fixing components as well as the shaft end. The cover also lends itself for a logo or other symbols.

The collet version permits a simple adjustment of the types with scale or arrow.

Besides the standard scale (Type S) the control knobs can be supplied with any type of graduation.

Regarding design, numbering run, numbering position and numbering sequence of the scale please see the layout for scale knobs on the order sheet „How to order Graduations“ → Page 252

see also...

- Control knobs GN 723.4 (Aluminum) → Page 264
- Clamping elements GN 826 (for adjustable spindles) → Page 268

How to order

GN 726.2-27-Z6-S-2

- | | |
|---|----------------------------------|
| 1 | d ₁ |
| 2 | d ₃ (d ₂) |
| 3 | Type |
| 4 | Identification no. |