



**2 Type**

- A** Mounting from the back (threaded blind bore)
- B** Mounting from the operator's side



$l_1 \pm 0,25$ GN 728	$l_1 \pm 0,25$ GN 728.5	b	d <sub>1</sub>	d <sub>2</sub>	d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>	l <sub>2</sub>	l <sub>3</sub>	s	t <sub>1</sub> min.	t <sub>2</sub>
120	120	22,5	M 6	6,4	11	42,5	6,5	147	108	8	10	6,5
180	-	27	M 8	8,4	13,5	47,5	7,5	214	165	10	12	8,5

**Specification**

- **GN 728**  
Aluminum pressure die casting
  - plastic coated
  - black, RAL 9005, textured finish
  - silver, RAL 9006, textured finish
  - blank
  - tumbled
- **GN 728.5**  
Stainless Steel AISI CF-8
  - Precision casting
  - matte shot-blasted
- Load rating information → Page 1458
- Stainless Steel characteristics → Page 1489
- RoHS



**Information**

The installation of cabinet U-handles GN 728 / GN 728.5 can be carried out from the back (Type A) as well as from the operator's side (Type B).

see also...

- Product family Standard Parts for profile systems → Page 20
- Cabinet U-handles GN 528  
(Plastic, mounting from the operator's side) → Page 90
- Cabinet U-handles GN 528.1  
(Plastic, mounting from the back) → Page 91
- Assembly sets for profile systems 30 / 40 GN 965 → Page 1428
- Assembly sets for profile systems 30 / 40 / 45 GN 968 → Page 1438

How to order (Aluminum)

**GN 728-120-A-SW**

- 1  $l_1$
- 2 **Type**
- 3 **Finish**

How to order (Stainless Steel)

**GN 728.5-120-B**

- 1  $l_1$
- 2 **Type**