



<b>1</b> d <sub>1</sub>	<b>2</b> d <sub>2</sub>	<b>3</b> Length l					d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>	s	max. thread length for internal thread
34	M 6	11	15	20	25	30	16	21	10,5	5	19
42	M 8	15	20	25	30	40	19	26	13	5	24
42	M 8 x 1	15	20	25	30	-	19	26	13	5	24
53	M 10	20	25	30	40	50	24	32	16	5	30
53	M 10 x 1	20	25	30	40	-	24	32	16	5	30

### Specification

- Plastic  
Technopolymer (Polyamide PA)  
- glass fiber reinforced  
- temperature resistant up to 130 °C  
- black, matte finish
- Threaded inserts  
- Steel **ST**  
zinc plated, blue passivated  
- Stainless Steel AISI 304 **NI**
- Cover cap plastic  
light gray, matte
- *Plastic characteristics* → Page 1483
- *Stainless Steel characteristics* → Page 1489
- **RoHS**

### On request

- Cover cap in further colors  
(standard color: light gray)



### Information

Knurled knobs / Knurled screws GN 7336 distinguish an attractive design in combination with closed shape (no recess on the underside of the handles).

Knurled knobs GN 7336 are also available without threaded insert.

How to order:

- GN 7336-34
- GN 7336-42
- GN 7336-53

see also...

- *Knurled knobs GN 534* → Page 442
- *Knurled screws GN 534* → Page 443

How to order (Bushing)

**GN 7336-42-M8-NI**

<b>1</b>	d <sub>1</sub>
<b>2</b>	d <sub>2</sub>
<b>4</b>	Material

How to order (Threaded stud)

**GN 7336-34-M6-20-ST**

<b>1</b>	d <sub>1</sub>
<b>2</b>	d <sub>2</sub>
<b>3</b>	Length l
<b>4</b>	Material