



Rost frei Inox Stainless Steel

- 4 Type**
- MS** Brass pivot
 - KU** Plastic pivot (Polyacetal POM)
 - ZK** spherical pivot

1 2 3

d ₁	d ₂	l ₁				d ₃	d ₄	d ₅	d ₆ +0,05	h ₁	h ₂	l ₂	l ₃	l ₄ ≈	
34	M 6	6	15	20	25	30	16	4	3,5	4,5	21	10,5	1	1,3	5,1
42	M 8	8	20	25	30	40	19	6	5	6,1	26	13	1,5	1,6	6,2
53	M 10	10	25	30	40	50	24	8	6,5	7,8	32	16	2	1,9	7,3

Specification

- Plastic Technopolymer (Polyamide PA)
 - glas fiber reinforced
 - temperature resistant up to 130 °C
 - black, matt
- Threaded stud Stainless Steel AISI 304
- Cover cap plastic light gray, matte
- *Plastic characteristics* → Page 1483
- *Stainless Steel characteristics* → Page 1489
- RoHS

Information

Knurled screws GN 7336.5, type MS / KU with brass or plastic pivots are used when pressure dents or damage must be avoided.

Knurled screws GN 7336.5, type ZK feature a spherical pivot whose Ø d₆ is smaller than the core Ø of the thread. The version with spherical pivot is suitable for holding GN 631 / GN 631.5 thrust pads, which must be ordered separately.

The knurled screws GN 7336.5 distinguish an attractive design in combination with closed shape (no recess on the underside of the handles).

see also...

- *Thrust pads (Plastic) GN 631* → Page 798
- *Stainless Steel-Thrust pads GN 631.5* → Page 798
- *Star knobs GN 6336.10 (with brass / plastic pivot)* → Page 402
- *Star knobs GN 6336.12 (with movable thrust pad)* → Page 403
- *Knurled screws GN 421.10 (with brass / plastic pivot)* → Page 450
- *Knurled screws GN 421.12 (with movable thrust pad)* → Page 451

How to order

1	d ₁
2	d ₂
3	l ₁
4	Type

GN 7336.5-42-M8-25-MS

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

