



**3 Type**

- D** with female thread
- E** with threaded rod

<b>1</b> d <sub>1</sub>	<b>2</b> d <sub>2</sub> Type D	<b>2</b> d <sub>3</sub> Type E	d <sub>4</sub>	h	Length l	t min.
16	M 5	M 6	10	18	10	7
20	M 6	M 8	12	24	12	9
25	M 6	M 8	14	29	14	9
32	M 8	M 10	18	37	16	12
36	M 10	M 12	20	42	18	15

\* usually not available from stock, requires a minimum order quantity

**Specification**

- **GN 75**  
Steel  
- fine turned  
- blackend
  - **GN 75.5**  
Stainless Steel  
- AISI 304  
- matte shot-blasted  
- highly polished
- MT**  
**PL \***
- *Stainless Steel characteristics* → Page 1489
- **RoHS**

**On request**

- Steel, zinc plated
- Stainless Steel (A4 quality)

**Information**

Waist shaped knobs GN 75 boast a compact and timeless design.

Waist shaped knobs GN 75.5 are made of high-grade stainless steel which makes them the first choice when it comes to applications requiring high standards of hygiene. The favourably designed and non-scooped geometry helps to prevent damp and the related risk of dirt collecting.

**see also...**

- *Knobs GN 676.1 (Steel, blackened)* → Page 64
- *Stainless Steel-Knobs GN 676.5* → Page 64

How to order (Steel) <b>GN 75-25-M6-D</b>	<b>1</b> d <sub>1</sub>
	<b>2</b> d <sub>2</sub> (d <sub>3</sub> )
	<b>3</b> Type

How to order (Stainless Steel) <b>GN 75.5-25-M8-E-MT</b>	<b>1</b> d <sub>1</sub>
	<b>2</b> d <sub>3</sub> (d <sub>2</sub> )
	<b>3</b> Type
	<b>4</b> Finish

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4

