



3 Type

- D** With internal thread
- E** With threaded stud

1 d ₁	2 d ₂ Type D	2 d ₃ Type E	d ₄	h	Length l	t min.
16	M 5	M 6	10	18	10	7
20	M 6	M 8	12	24	12	9
25	M 6	M 8	14	29	14	9
32	M 8	M 10	18	37	16	12
36	M 10	M 12	20	42	18	15

* usually not available from stock, requires a minimum order quantity

Specification

- **GN 75**
Steel
- Fine turned
- Blackend
- **GN 75.5**
Stainless steel AISI 304
- Matte shot-blasted **MT**
- Highly polished **PL***
- *Stainless Steel Characteristics* → Page 2166
- **RoHS**

On request

- Version in steel, zinc plated
- Version in stainless steel (A4 quality)



Information

Waist shaped knobs GN 75 / GN 75.5 have a compact and timeless design.

Waist shaped knobs GN 75.5 are made of high-grade stainless steel which makes them the first choice when it comes to applications requiring high standards of hygiene. The favourably designed and non-scooped geometry helps to prevent damp and the related risk of dirt collecting.

see also...

- *Knobs GN 676.1 (Steel, Blackened)* → Page 88
- *Stainless Steel Knobs GN 676.5* → Page 88

How to order (Steel)	1 d ₁
1 2 3 GN 75-25-M6-D	2 d ₂ (d ₃)
	3 Type

How to order (Stainless steel)	1 d ₁
1 2 3 4 GN 75.5-25-M8-E-MT	2 d ₃ (d ₂)
	3 Type
	4 Finish