



ROSTFREI  
Inox  
Stainless  
Steel

3.1

3.2

3.3

3.4

<sup>1</sup> d <sub>1</sub> H9	<sup>2</sup> d <sub>2</sub>	d <sub>3</sub>	d <sub>4</sub>	Length l	r	s -0,2	t min.	w min.
6	M 6	10	14	22	8,5	6	12	218°
8	M 8	14	18	29	12	8	16	218°
10	M 10	18	23	35	14	10	20	212°
12	M 12	20	27	43	17	12	24	216°
14	M 14	24	30	50	19	14	28	214°
16	M 16	26	36	56	22	16	32	216°

3.5

3.6

**Specification**

- Steel -
- Tensile strength class 5
- zinc plated, blue passivated
- Stainless Steel AISI 303 **NI**
- Strength values of nuts → Page 1481
- ISO-Fundamental tolerances → Page 1479
- Stainless Steel characteristics → Page 1489
- RoHS

<sup>3</sup>

**Information**

Joints pieces GN 752 are designed to be used in combination with fork heads DIN 71752 respectively fork joints GN 751.

see also...

- Swing nuts GN 444.2 → Page 806
- Fork head DIN 71752 (Steel) → Page 1160
- Fork joints GN 751 (Steel) → Page 1160

3.7

3.8

3.9

How to order (Steel)	1	d <sub>1</sub>
<sup>1</sup> <sup>2</sup> <b>GN 752-10-M10</b>	2	d <sub>2</sub>

How to order (Stainless Steel)	1	d <sub>1</sub>
<sup>1</sup> <sup>2</sup> <sup>3</sup> <b>GN 752-8-M8-NI</b>	2	d <sub>2</sub>
	3	Material

