



**3 Type**

- D** With internal thread
- E** With threaded stud

<b>d<sub>1</sub></b>	<b>d<sub>2</sub></b> Type D	<b>d<sub>3</sub></b> Type E	<b>d<sub>4</sub></b>	<b>d<sub>5</sub></b>	<b>h</b>	<b>Length l</b>	<b>t</b> min.
20	M 5	M 5	14	14,8	24	10	7
25	M 6	M 6	16	16,8	29	12	9
32	M 8	M 8	18	18,8	37	14	12

**Specification**

- Stainless steel AISI 316L
  - Matte finish (Ra < 0,8 µm) **MT**
  - Polished finish (Ra < 0,8 µm) **PL**
- Sealing ring
  - H-NBR **H**  
Temperature resistant -25 °C to +150 °C
  - EPDM **E**  
Temperature resistant -40 °C to +120 °C
  - Blue
  - Hardness 85 ±5 Shore A
  - FDA compliant
- *Elastomer Characteristics* → Page 2158
- *Stainless Steel Characteristics* → Page 2166
- RoHS

**Information**

Waist shaped stainless steel knobs GN 75.6 are intended for use in hygienic areas. The sealed mounting surface enables mounting without dead spaces; the impervious geometry in combination with the high quality finish prevents the accumulation of dirt and facilitates cleaning.

Waist shaped stainless steel knobs GN 75.6 have a compact and timeless design.

see also...

- *Product Family Hygienic Design* → Page 16

**Accessory**

- Sealing Rings GN 7600 → Page 1596

How to order	1	d <sub>1</sub>
	2	d <sub>3</sub> (d <sub>2</sub> )
	3	Type
	4	Finish
	5	Material (Sealing ring)

**GN 75.6-25-M6-E-MT-H**

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4

