



ROSTFREI
Inox
Stainless
Steel

1.1
1.2
1.3
1.4

d ₁		d ₂		d ₃	d ₄	l ₁	l ₂	l ₃ ≈	l ₄
KT	NI								
16	-	M 6	-	10	13	41,5	12	2,5	15
18	18	M 6	M 8	10	14,5	56	13	2,5	19
22	22	M 8	M 10	14	18,5	59	14	2,5	21
24	24	M 8	M 10	14	18,5	74	16	2,5	27
25	-	M 10	-	16	20	84	16	2,5	30

Specification

- Plastic **KT**
Technopolymer (Polyamide PA)
- Temperature resistant up to 90 °C
- Black, matte finish
- Stainless steel AISI 303 **NI**
Fine turned, plain
- Spindle
Stainless steel AISI 303
- *Plastic Characteristics* → Page 2158
- *Stainless Steel Characteristics* → Page 2166
- RoHS

Information

Typical in design are the revolving handles GN 798.1 with their stepped shape consisting of two cylinders giving the operator a better grip.
 see also...
 • *Retractable Handles GN 798.5 (with Hold in Both Positions)* → Page 52

2.1
2.2
2.3
2.4

How to order	1	Material
	2	d ₁
	3	d ₂

GN 798.1-KT-16-M6