



1

2

d <sub>1</sub>	Length l				d <sub>2</sub>	e	h	m
M 5*	37	-	-	-	14	-	10	4,7
M 6	32	42	52	-	12	2,2	7	5,2
M 8	38	48	63	83	16	3	9	6,8
M 10	44	54	64	84	20	3,6	11	8,4
M 12	55	65	85	105	25	4,5	13	10,8

\* Clamping bolt M5: bolt end and thrust pad are not hardened and not removable.

## Specification

- Screw DIN 6332 → Page 793  
Steel
  - Thrust point hardened (type SK)
  - blackened
- Thrust pad DIN 6311 → Page 794  
Steel  
case hardened
- Hexagon nuts ISO 4032 / DIN 934  
Steel  
zinc plated, blue passivated
- RoHS

## Information

By means of the retaining ring in the thrust pad a simple and toggle link between screw and thrust pad is created.

The two hexagon nuts are included parts of the order.

see also...

- *Holders for clamping screws GN 809*  
(for toggle clamps with solid clamping arm) → Page 591
- *Holders for clamping screws GN 801*  
(for toggle clamps with forked clamping arm) → Page 590

How to order

GN802-M8-48

1 d<sub>1</sub>

2 Length l