



Protective cap GN 806



3 Type

- A** without protective cap
- B** with protective cap

1

2

d ₁					d ₂	h ₁	h ₂	l ₂	m	A/F
Steel	Stainless Steel	l ₁								
M 4	M 4	23	-	-	11	3	6,5	2,5	3,2	7
M 5	M 5	38	-	-	12,5	3,5	8	2,5	4,7	8
M 6	M 6	29	49	-	15	4	10	4	5,2	10
M 8	M 8	36	56	96	19	5,5	13	5,5	6,8	13
M 10	-	43	77	127	24	6,5	16	7	8,4	16
M 12	-	53	88	128	26	7,5	19	8,5	10,8	18
M 14*	-	54	-	-	-	9	-	-	12,8	21

* Clamping screw M14 is not available as type B (with protective cap)

Specification

4

- Steel —
 - Hexagon head screw ISO 4017 / DIN 933
 - Tensile strength class 8.8
 - zinc plated, blue passivated
 - Hexagon nuts ISO 4032
 - zinc plated, blue passivated
- Stainless Steel AISI 304 **NI**
 - Hexagon head screw ISO 4017 / DIN 933
 - Hexagon nuts ISO 4032
- Protective caps GN 806 → Page 1089
- Stainless Steel characteristics → Page 1489
- RoHS

Information

The two hexagon nuts are included parts of the order.

see also...

- Holders for clamping screws GN 809 (for toggle clamps with solid clamping arm) → Page 591
- Holders for clamping screws GN 801 (for toggle clamps with forked clamping arm) → Page 590

How to order (Steel)

GN807-M8-56-B

1	d ₁
2	l ₁
3	Type

How to order (Stainless Steel)

GN807-M6-29-A-NI

1	d ₁
2	l ₁
3	Type
4	Material