



elesa

ELESA Original design BAG2-120

Inox
Stainless
Steel

1

2

d ₁ Bore B	d ₂ Bore B		for tube outside-Ø	standard description in inch
B 42,4	B 42,4	-	42,4	1 1/4"
B 48,3	B 42,4	B 48,3	48,3	1 1/2"
B 60,3	B 42,4	B 48,3	60,3	2"

Specification

- Plastic (Polyamide PA)
 - glass fiber reinforced
 - temperature resistant up to 100 °C
 - black, matte
- Hexagon screws DIN 931
Stainless Steel AISI 304
- Hexagon nuts DIN 934
Stainless Steel AISI 304
- Washers
Stainless Steel AISI 304
- *Stainless Steel characteristics* → Page XYZ
- *Plastic characteristics* → Page XYZ ff.
- RoHS

Information

see also...

- *Levelling feet* → Page XYZ ff.
- *Construction tubes GN 990* → Page XYZ

How to order

GN84-B60,3-B42,4

1 d₁2 d₂