



ELESA Original design TTA. / TTB.



2 Type

- D** Fixing with slotted holes
- E** Fixing with bores

| 1 | | 1 | |
|----------|--------|--------------------|------------------------------|
| d | | for tube outside-Ø | standard description in inch |
| Bore B | | | |
| Type D | Type E | | |
| B 42,4 | - | 42,4 | 1 1/4" |
| B 48,3 | B 48,3 | 48,3 | 1 1/2" |
| B 60,3 | - | 60,3 | 2" |

Specification

- Plastic (Polyamide PA)
 - glass fiber reinforced
 - temperature resistant up to 100 °C
 - black, matte
- Hexagon screws DIN 931
Stainless Steel AISI 304
- Hexagon nuts DIN 934
Stainless Steel AISI 304
- Washers
Stainless Steel AISI 304
- *Stainless Steel characteristics* → Page XYZ
- *Plastic characteristics* → Page XYZ ff.
- RoHS

On request

- Type D with square 45 x 45

Information

see also...

- *Base plate connector clamps GN 163 (Aluminium)* → Page XYZ
- *Construction tubes GN 990* → Page XYZ

| | |
|---------------------|---------------|
| How to order | 1 d |
| | 2 Type |

GN86-B48,3-E

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9