



Swing clamp GN 876



| for swing clamps Size | ² d ₁ | ³ m | d ₂ | h | Length l |
|-----------------------|-----------------------------|----------------|----------------|----|----------|
| 25 | M 40x1,5 | 37 | 5,4 | 9 | 50 |
| 32 | M 50x1,5 | 45 | 6,6 | 12 | 60 |
| 40 | M 55x1,5 | 50 | 6,6 | 12 | 65 |
| 50 | M 65x1,5 | 58 | 9 | 15 | 75 |
| 63 | M 80x1,5 | 70 | 9 | 15 | 88 |

Specification

- Steel zinc plated, blue passivated
- RoHS

¹ **ST**

Information

Threaded flanges GN 876.1 designed as accessories to swing clamps GN 876.

This makes it unnecessary to tap the mounting hole of the part.

see also...

- *Swing clamps GN 876 (pneumatic, with screw-in thread) → Page 60*

| | |
|-------------------------------|-----------------------------------|
| How to order | ¹ Material |
| GN 876.1-ST-M55x1,5-50 | ² d₁ |
| | ³ m |