



**2 Type**

- A** Connector straight
- B** Connector 45°
- C** Connector 90°

**1**

**3**

Size	d <sub>1</sub> Connection thread for GN 880	Length l Hose length			d <sub>2</sub> Nipple	d <sub>3</sub> Nominal width Hose
22	M 22 x 1,5	250	500	1000	15	14
26	M 26 x 1,5	250	500	1000	20	19

**Specification**

- Connecting nut with hose liner  
Brass
- L bend 45° / 90°  
Copper
- O-Ring  
Rubber NBR (Perbunan)
- Drain hose  
PVC, transparent **T**
- Hose clip  
Steel, zinc plated
- Plug  
Plastic, LD-PE
- **RoHS**

**On request**

- other hose length
- Drain hose with inside webbing (Nylon)

**4**

**Information**

Connector pieces GN 880.1 are needed when using oil drain valves GN 880.

Screwing on the connector piece will activate the valve plate of the oil drain valve, allowing the oil to flow through the hose into a pan held ready.

The plug prevents remaining oil from dripping out after discharging.

see also...

- *Oil drain valves GN 880* → Page 1122

How to order (without drain hose)	<b>1</b> Size
<b>GN880.1-26-C</b>	<b>2</b> Type

How to order (with drain hose)	<b>1</b> Size
<b>GN880.1-22-A-500-T</b>	<b>2</b> Type
	<b>3</b> Length of the hose
	<b>4</b> Type of the hose

3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9

