



2 Type
A Connector straight
B Connector 45°
C Connector 90°

Size	d ₁ Connection thread for GN 880	Length l Hose length			d ₂ Hose liner	d ₃ Nominal width Hose	d ₄ ≈
22	M 22 x 1,5	250	500	1000	15	14	15,5
26	M 26 x 1,5	250	500	1000	20	19	20

Specification

- Connecting nut with hose liner
Brass
- L bend 45° / 90°
Copper
- O-Ring
Rubber NBR (Perbunan®)
- Drain hose
PVC, transparent **T**
- Hose clip
Steel, zinc plated
- Plug
Plastic, PE-LD
- *Elastomer characteristics* → Page 1483
- *Plastic characteristics* → Page 1483
- **RoHS**

On request

- other hose length
- Drain hose with inside webbing (Nylon)

Information

Connector pieces GN 880.1 are needed when using oil drain valves GN 880.

Screwing on the connector piece will activate the valve plate of the oil drain valve, allowing the oil to flow through the hose into a pan held ready.

The plug prevents remaining oil from dripping out after discharging.

see also...

- *Oil drain valves GN 880* → Page 1122

How to order (without drain hose)	1	Size
	2	Type

GN880.1-26-C

How to order (with drain hose)	1	Size
	2	Type
	3	Length of the hose
	4	Type of the hose

GN880.1-22-A-500-T

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9