



ROSTFREI
Inox
Stainless
Steel



d ₁		l ₂	d ₂	l ₁	l ₃	l ₄	h ₁	h ₂
GN 911	GN 911.3							
M 6	M 6	22	9,9	45	19	3	24,5	35
M 6	-	25	9,9	45	22	3	24,5	35
M 6	-	32	9,9	45	29	3	24,5	35
M 8	-	32	12,9	63	27,5	4,5	31	45
M 8	-	35	12,9	63	30,5	4,5	31	45
M 8	-	40	12,9	63	35,5	4,5	31	45
M 8	-	45	12,9	63	40,5	4,5	31	45
M 8	-	50	12,9	63	45,5	4,5	31	45
M 8	-	55	12,9	63	50,5	4,5	31	45
M 10	-	40	16,9	78	34,5	5,5	36	55
M 10	-	50	16,9	78	44,5	5,5	36	55
M 10	-	55	16,9	78	49,5	5,5	36	55
M 10	-	63	16,9	78	57,5	5,5	36	55
M 10	-	70	16,9	78	64,5	5,5	36	55
M 10	-	80	16,9	78	74,5	5,5	36	55

Specification

- **GN 911**
Handle
Zinc die casting
plastic coated
silver, RAL 9006, textured finish
- **GN 911.3**
Handle
Stainless Steel precision casting
- AISI CF-8
- matte shot-blasted
- Threaded stud / Distance bushing
Stainless Steel AISI 303
- *Stainless Steel characteristics → Page 1489*
- **RoHS**

Information

The clamping kits GN 911 / GN 911.3 replace the hexagon socket screws DIN 912 of the connector clamps.

The table of dimensions of the connector clamps shows the corresponding clamping kits for each clamping thread.

The distance bushing is included part of the order.

How to order (Lever zinc die casting)	1	d ₁
	2	l ₂
GN911-M8-45		

How to order (Stainless Steel)	1	d ₁
	2	l ₂
GN911.3-M6-22		