



Rostfrei  
Inox  
Stainless  
Steel

d	b <sub>1</sub>	b <sub>2</sub>	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	Length l	r <sub>1</sub>	r <sub>2</sub>	s Stroke cam	r <sub>2</sub> -h <sub>3</sub> Total stroke
8	13	9	19,54	14	12	114	17,2	21,07	3,87	9,07
10	17	12	24,54	17	15	138	21,6	26,45	4,85	11,45
12	20	14	31,81	21	18	157	28	34,29	6,29	16,29

**Specification**

- **GN 917**  
Steel  
- ST 52-3 / German Material No. 1.0570  
- blackened
- **GN 917.1**  
Stainless Steel AISI 304  
shot-blasted

This information applies to both standards:

- King pin  
Stainless Steel AISI 420  
tempered
- Circlip  
Stainless Steel AISI 301
- Plastic cover  
- red, oil resistant  
- temperature resistant up to 60 °C
- *Stainless Steel characteristics* → Page 1489
- **RoHS compliant**

**Information**

Double cam levers GN 917 / GN 917.1 are used for repositioning and clamping.

The eccentric cam has the advantage that the clamping force remains constant in every position of its travel and in addition is self arresting.

The dimension b<sub>2</sub> is made to match the head size of swing bolts DIN 444 and swing nuts GN 444.2 respectively.

see also...

- *Swing bolts DIN 444* → Page 776
- *Swing nuts GN 444.2* → Page 806
- *Eccentric cams GN 918* → Page 472

How to order (Steel) GN917-10-17	1	d
	2	b <sub>1</sub>

How to order (Stainless Steel) GN917.1-12-20	1	d
	2	b <sub>1</sub>

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4

