



ROSTFREI  
Inox  
Stainless  
Steel

- 2 Bore code**  
B without keyway  
K with keyway
- 4 Type**  
A without handle  
D with revolving handle

d <sub>1</sub>	d <sub>2</sub> H8 Bore		d <sub>3</sub>	b	l <sub>1</sub>	l <sub>2</sub> ≈	l <sub>3</sub> ≈	r	Ø Handle	No. of spokes
	1	3								
100	10	12	20	7	15	27,5	45	44	18	3
125	12	14	24	9	16	28,5	55	55	21	3
140	14	16	28	10	18	30,5	70,5	62	23	3
160	14	16	31	11	20	35,5	70,5	71	23	3
200	18	20	36	14	23	39	70,5	90	23	3

**Specification**

- Stainless Steel precision casting
  - AISI CF-8
  - Hub machined
  - Rim turned
  - matte shot-blasted
- Revolving handles similar to GN 598.1
  - Plastic, Duroplast black, shiny
  - Spindle Stainless Steel AISI 304
- Keyway P9 DIN 6885 → Page 1420
- Cross holes GN 110 → Page 1422
- Stainless Steel characteristics → Page 1489
- RoHS

**Information**

The design of Stainless Steel-Handwheels GN 949 complies with the requirements of hygiene standards.

The revolving handles are made of duroplast which, in general, provides good resistance to the impact of chemical agents.

see also...

- *Stainless Steel-Countersunk washers GN 184.5 (for axial fixing)* → Page 814

How to order	1	d <sub>1</sub>
	2	Bore code
	3	d <sub>2</sub>
	4	Type
GN 949 - 125 - B12-A		

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4