



ROSTFREI  
Inox  
Stainless  
Steel

1 2 3

d <sub>1</sub>	b	l <sub>1</sub>	d <sub>2</sub>	l <sub>3</sub>	Size	GN 851		GN 851.3		Size	GN 851.1		GN 851.2	
						r at w <sub>2</sub> =0	w <sub>2</sub>	r at w <sub>2</sub> =0	w <sub>2</sub>		r at w <sub>2</sub> =0	w <sub>2</sub>	r at w <sub>2</sub> =0	w <sub>2</sub>
M 4	21	56*	3,4	27,5	160	35	11	35	11	-	-	-	-	-
M 4	21	70**	3,4	28,5	160	48	12	48	12	160	50	12	160	12
M 4	21	103	3,4	30	160	80	14	80	14	160	82	14	160	14
M 4	21	153	3,4	35	160	125	19	125	19	160	127	19	160	19
M 4	21	203	3,4	35	160	175	19	175	19	160	177	19	160	19
M 6	32	78*	5,2	33	320	57	10	54	13	-	-	-	-	-
M 6	32	110**	5,2	44	320	75	24	75	24	320	78	21	320	21
M 6	32	130	5,2	45	320	94	25	94	25	320	94	25	320	25
M 6	32	155	5,2	45	320	119	25	119	25	320	119	25	320	25
M 6	32	205	5,2	45	320	169	25	169	25	320	169	25	320	25
M 8	38	111*	7,2	52	700	74	22	70	26	-	-	-	-	-
M 8	38	127	7,2	60	700	78	34	78	34	-	-	-	-	-
M 8	38	143**	7,2	56	700	98	30	98	30	700	98	30	700	30
M 8	38	157	7,2	60	700	108	34	108	34	700	108	34	700	34
M 8	38	207	7,2	60	700	158	34	158	34	700	158	34	700	34

\* These U-bolt latch lengths are included in the delivery of standard orders for GN 851 / GN 851.3.

\*\* These U-bolt latch lengths are included in the delivery of standard orders for GN 851.1 / GN 851.2.

**Specification**

- Steel **ST**
- zinc plated, blue passivated
- Stainless Steel AISI 304 **NI**
- Hexagon nuts (with polyamide insert)  
M4: DIN 934 / DIN 985  
M6 / M8: DIN 936 / DIN 985  
Steel, zinc plated resp. Stainless Steel
- *Stainless Steel characteristics* → Page 1489
- RoHS

**On request**

- Stainless Steel AISI 316 **A4**

**Information**

see also...

- *Horizontal latch type toggle clamps GN 851* → Page 542
- *Stainless Steel-Horizontal latch type toggle clamps GN 851* → Page 542
- *Vertical hook type toggle clamps GN 851.1* → Page 546
- *Stainless Steel-Vertical hook type toggle clamps GN 851.1* → Page 546
- *Latch type toggle clamps GN 851.2* → Page 548
- *Latch type toggle clamps GN 851.3* → Page 544
- *Stainless Steel-Latch type toggle clamps GN 851.3* → Page 544

**How to order**

1	d <sub>1</sub>
2	b
3	l <sub>1</sub>
4	Material

**GN 951.1-M6-32-130-NI**