



b	d₁ ^{+0.06 +0.02}						d₂	l₁	l₂	l₃	l₄	m₁	m₂	for position indicators
33	B 8 B 10 B 12 B 14	-	4,5	47	30,5	11	22	21	23,5	GN 954 / GN 9054				
48	B 12 B 14 B 15 B 16 B 20	5,5	67	43,1	16	22	34	33,6	GN 953 / GN 9053 / GN 9153					

Specification

- Zinc die casting plastic coated black, textured finish
- Adjustable hand levers GN 302-30 black, RAL 9005, textured finish → Page 335
- RoHS

Information

Clamping plates GN 953.6 / GN 954.6 are used in connection with position indicators GN 953, GN 954, GN 9053, GN 9153 and GN 9054.

In a simpler way and without large construction and installation effort these spindles can, after adjustment, be clamped and locked.

At the same time these plates are fitted with the bore Ø 6,1 to accept the torque limiter for the position indicator.

The spacer can be installed so that it lies as required either to the right or the left.

How to order (for GN 953 / GN 9053 / GN 9153)	1	b
GN953.6-48-B12	2	d₁

How to order (for GN 954 / GN 9054)	1	b
GN954.6-33-B10	2	d₁