



d Ø	w	l ₁	l ₂	for tube
D 10	1 ... 2	3,5	11	GN 990
D 12	1 ... 2	3,5	11	GN 990
D 13	1 ... 2	4	11	¼"
D 14	1 ... 2	5	11,5	GN 990
D 15	1 ... 2	3	11,5	GN 990
D 16	1 ... 2	5	11	GN 990
D 18	1 ... 2	5	11,5	GN 990
D 20	1 ... 2,5	5	11,5	GN 990
D 22	1 ... 2	5	11,5	-
D 25	1 ... 3	5	11,5	GN 990
D 26	1 ... 3	5	11,5	-
D 27	1 ... 3	5	11,5	¾"
D 28	1 ... 3	5	11,5	-
D 30	1 ... 2,5	5	11,5	GN 990
D 32	1 ... 3	5	12	GN 990
D 34	1 ... 3	5	11,5	1"

d Ø	w	l ₁	l ₂	for tube
D 35	1 ... 3	5	11,5	GN 990
D 36	1 ... 3	5	11,5	-
D 38	1 ... 3,5	5	11,5	-
D 40	1 ... 3	5	11,5	GN 990
D 42	1 ... 3	5	11,5	GN 990
D 45	1 ... 3	5	11	GN 990
D 48	1,2 ... 3,6	5	11,5	GN 990
D 50	2,5 ... 4,5	5	11,5	GN 990
D 55	3 ... 5	5	14,5	GN 990
D 60	3 ... 5	5	17,5	GN 990
D 70	1,5 ... 3,5	5	21	-
D 76	1,6 ... 4	6	21,5	2 ½"
D 80	1,5 ... 3	5	22	-
D 88	1,5 ... 4	6	21,5	3"
D 90	1,5 ... 5	6	21	-
D 100	2 ... 4,5	6	28,5	-

s ∅	w	l ₁	l ₂	for tube
V 10	0,8 ... 2,5	4	12	GN 990
V 12	1 ... 2	4	12	GN 990
V 15	1 ... 2	3	11,5	-
V 16	1 ... 2,5	5	11,5	GN 990
V 18	1,5 ... 3	5	11,5	-
V 20	1 ... 3	5	11,5	GN 990
V 22	1 ... 3,5	5	12	-
V 25	1 ... 3	5	11,5	GN 990
V 30	1 ... 3	5	11,5	GN 990
V 34	1 ... 3	5	14,5	-
V 35	1 ... 3	5	11,5	GN 990
V 40	1 ... 3	5	14,5	GN 990
V 45	1 ... 3	5	14,5	GN 990
V 50	2,6 ... 4	5,5	24	GN 990
V 55	2 ... 4,5	5	14,5	-
V 60	1,5 ... 3,5	5	15	-
V 70	2 ... 5	5	22	-
V 80	1,5 ... 4	6	21	-
V 90	3 ... 5	6	21	-
V 100	1 ... 4	7	21	-

Specification

- Plastic Technopolymer (Polyethylen PE)
 - black, RAL 9005, matt ● SW
 - grey, RAL 7042, matt ● GR
- Plastic characteristics → Page 1489
- RoHS compliant

On request

- other sizes
- white (WS)

Information

Tube end plugs GN 991 have been designed for sealing tube ends for safety or optical reasons.

They are pressed into the tube end either by hand or with a mallet.

see also...

- Construction tubes GN 990 → Page 1277
- Retaining rods / Retaining tubes GN 480.1 → Page 1276
- Insert bushings GN 992 (Aluminum, with female thread) → Page 1059

How to order GN991-V25-GR	1 s (d)
	2 Color