



1 d min.	2 d max.	Länge I	b
A 16	20	110	3
A 25	28	136	4
A 30	32	136	4
A 34	36	170	5
A 40	42	170	5
A 45	50	206	6
A 52	55	206	6
A 58	62	240	7
A 65	70	240	7
A 68	75	240	7
A 80	90	280	8
A 95	100	280	8

AusführungStahl
brüniert

RoHS

Hinweise

DIN 70852 Nutmuttern	QVX
GN 1804.2 Nutmuttern	QVX
GN 1804.1 Nutmuttern	QVX
DIN 1804 Nutmuttern (Stahl / Edelstahl)	QVX
GN 350 Ausgleich-Elemente	QVX
GN 350.5 Ausgleich-Elemente	QVX
GN 350.1 Ausgleich-Elemente	QVX
GN 350.2 Ausgleich-Elemente	QVX
GN 360 Ausgleich-Stellfüße (Stahl / Edelstahl)	QVX

Bestellbeispiel
DIN 1810-A34-36
1 d min.**2** d max.