



1			2					
l_1			d_1	d_2	d_3	h_1	$h_2 \approx$	$l_2 \approx$
GN 99.5	GN 99.6	GN 99.6						
	1.4301	1.4404						
63	63	63	M 8	16	10	12,5	30,5	60
80	80	80	M 10	20	12	15	37	76
100	100	100	M 12	25	14	19	46	95
125	125	-	M 16	32	18	25	58,5	119
160	160	-	M 20	40	20	31	73	152

Ausführung

GN 99.5

Stahl
verzinkt, blau passiviert

GN 99.6

- Edelstahl 1.4301
- Edelstahl 1.4404
- matt gestrahlt

Schaft

stumpf aufgeschweißt

RoHS



Hinweise

DIN 99 Kegelgriffe (Stahl / Edelstahl)

GN 206 Spannmuttern (Stahlguss / Edelstahl-Feinguss)

Technische Informationen

Edelstahl-Eigenschaften

Seite

QVX

QVX

QVX

Bestellbeispiel (Stahl)

GN 99.5-100-M12

1	l_1
2	d_1

Bestellbeispiel (Edelstahl 1.4301)

GN 99.6-80-M10

1	l_1
2	d_1

Bestellbeispiel (Edelstahl 1.4404)

GN 99.6-80-M10-A4

1	l_1
2	d_1
3	Werkstoff

