



4 Profile type

L Light

1	2	3	6	7	s <sub>1</sub>	s <sub>2</sub>	n	Length l +1,5mm in meters	Bundle Pieces	d <sub>1</sub>	d <sub>2</sub> *	k	m <sub>1</sub>	m <sub>2</sub>	s <sub>3</sub>	t	Grid size
					40	40	10	2 3	4	10	5,5	-	29	29	6	12,5	40
					40	80	10	2 3	2	10	5,5	40	29	69	6	12,5	40
					45	45	10	2 3	4	10	-	-	-	-	6	14,5	45
					45	90	10	2 3	2	10	-	45	-	-	6	14,5	45
					80	80	10	2 3	1	10	5,5	40	69	69	6	12,5	40
					90	90	10	2 3	1	10	-	45	-	-	6	13	45

\* Bores only on grid size = 40

Specification

- Aluminum Anodized, natural color
- RoHS



Accessory

- T-Nuts GN 50b → Page QVX
- T-Slot Nuts GN 51b → Page QVX
- T-Slot Bolts GN 52b → Page QVX
- Cover Caps GN 60b → Page QVX
- Cover and Edging Profiles GN 70b → Page QVX
- Cover Profiles GN 71b → Page QVX
- Transport and Base Plates GN 80b → Page QVX

Information

Aluminum profiles GN 10b are produced by extrusion molding. They can be used, for example, to easily construct protective enclosures, work-place equipment or jigs.

Aluminum profiles in combination with the removable and reusable accessories form a flexible modular system. Attachments can be fastened to either the slots or the end faces via the holes.

The profile type light is typically used for small loads or for weight-optimized constructions.

Aluminum profiles are supplied in bundles. The table shows the quantity included in each bundle.

How to order

1	s <sub>1</sub>
2	s <sub>2</sub>
3	n
4	Profile type
5	Finish
6	Length l
7	Bundle

GN 10b-454510L-N-2-4

